

Super Polx[®] 1500

Cleanroom Laundered 100% Polyester Knit wiper

Super Polx[®] 1500 is a knife cut cleanroom laundered wiper recommended for ISO Class 4 and above environments composed of 100% continuous filament polyester knit fabric.

This combination of properties provides Super Polx[®] 1500 with the high level of cleanliness, abrasion resistance and chemical compatibility required for ISO Class 4 and above environments and

applications requiring critical control of contaminants combined with superior performance.



Key Attributes

- 100% continuous filament polyester knit
- Knife cut edge
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom

Benefits

- Low particles, fibers, ions and extractables
- High abrasion resistance
- Chemically compatible with IPA, Acetone and other solvents
- Light weight, high sorbency design
- Low endotoxin levels
- Soft hand and edge for sensitive surfaces

Environmental

- Complies with RoHS 2002/05 and REACH requirements
- Light weight, high absorbency design reduces landfill waste impact when compared to more traditional heavier weight fabrics

Other ISO Class 4 and above wipers

- Super Polx[®] 1200

Applications

- Designed for use in ISO Class 4 and higher cleanroom environments
- Designed for a high level of contamination control in critical processing applications
- Integrated circuit fabrication areas
- CD and DVD manufacturing operations
- Breakdown cleans in fab and suite construction
- Equipment wrap and wipe downs
- Stencil and other print roll cleaning applications
- Steam autoclavable for aseptic applications

Value Pack Option

The value pack option provides the same great performance in a more economical bulk packaging format.

Pre-Wetted Option

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs.

Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10⁻⁶ sterility assurance level. Dry and pre-wetted versions available.

www.berkshire.com

Contact: Tel 1 800 242 7000 / 1 413 528 2602
info@berkshire.com

America	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp

Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	131	TAPPI T-410
Caliper		μm	463	TAPPI T-411
Fibers	≥100μm	fibers/cm ²	1.7	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2
Particles	≥0.5μm	x10 ⁹ /cm ²	1.2	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.1
Sorbency	Capacity	mL/m ²	519	IEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	4.0	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.0088	IEST-RP.CC004.3, Sec 7.1.2
	IPA	g/m ²	0.013	
Ions	Na ⁺	ppm	0.13	IEST-RP.CC004.3, Sec 7.2.2
	K ⁺	ppm	ND	
	Ca ⁺⁺	ppm	0.044	
	Mg ⁺⁺	ppm	0.0059	
	Cl ⁻	ppm	0.16	

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
Super Polx® 1500	S1500.0909.8	9x9" (23x23cm)	150	8	Stacked
Super Polx® 1500	S1500.0909B.6	9x9" (23x23cm)	150	6	Value Pack

For more information on our other contamination control products or technical consultation, please contact your Berkshire Sales Representative or e-mail: info@berkshire.com

Other Berkshire products

For information on our other products, please click on the relevant text.



[Wipers](#)



[Glove Liners](#)




[Mop Systems](#)



[Documentation Systems](#)



[Face Masks](#)



[Swabs](#)